

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936014229

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect HE - Harsh Environment, Double Lever Bulkhead Housing, Die-cast Aluminum, with 2 Levers, with Cover, with Gasket, Size 32A «66x40», Black

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Component Size		32A «66x40»
Component Type		Double Lever Bulkhead Housing
IP Rating		IP66
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Type		HE
UPC		887191888958
Physical		
Cover Coating		Epoxy-Polyester Powder
Cover Color		Black RAL 9005
Housing Coating		Epoxy-Polyester Powder
Housing Color		Black RAL 9005
Lock to Mating Part		Yes
Material - Cover		Die-cast Aluminum
Material - Gasket		NBR
Material - Housing		Die-cast Aluminum
Material - Lever		Stainless Steel
Mounting Style		Bulkhead
Number of Levers		2
Packaging Type		Bag
Temperature Range - Operating		-25° to +125°C
Material Info		
Engineering Number		7832.4705.1

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

93601 Series

Use With

Power and Data Connecting Interfaces.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4229](#)