

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936014467

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect STD - Standard, Cover, Die-cast Aluminum, with 4 Pegs, without Gasket, Size 32B «77x62». Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93601</u>
Comments	With nylon wire tether line.
Component Size	32B «77X62»
Component Type	Cover
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191895635

Physical

Cover Coating	Polyester Powder
Cover Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	88.000/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	N/A
Thread Type	N/A

Electrical

Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number 7832.6808.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Use With

Size 32B «77x62» Housings with 2 Levers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4467