

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014532](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect HE - Harsh Environment, Single Lever Bulkhead Mount Housing, Die-cast Aluminum, with 1 Lever, with Cover, with Gasket, Size 48B «104x62», Black

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Component Size		48B «104x62»
Component Type		Single Lever Bulkhead Housing
IP Rating		IP66
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type		HE
UPC		887191829494
Physical		
Cover Coating		Polyester Powder
Cover Color		Black RAL 9005
Housing Coating		Polyester Powder
Housing Color		Black RAL 9005
Lock to Mating Part		Yes
Material - Cover		Die-cast Aluminum
Material - Gasket		NBR
Material - Housing		Die-cast Aluminum
Material - Lever		Stainless Steel
Mounting Style		Bulkhead
Net Weight		615.000/g
Number of Levers		1
Packaging Type		Bag
Thread Size		N/A
Thread Type		N/A
Electrical		
Voltage - Maximum		500V
Material Info		
Engineering Number		7848.6411.1



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

Use With
Size 48B «104x62» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-K and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4532](#)