

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

**Part Number:** 0936014581

**Status:** **Active**

## Overview: GWconnect Heavy Duty Connectors (HDC)

**Description:** GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Size 48B «104x62», without Threaded Opening, High Construction, Grey

### Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

### Agency Certification

|     |         |
|-----|---------|
| CSA | 256883  |
| UL  | E249674 |

## General

|                  |                                                         |
|------------------|---------------------------------------------------------|
| Product Family   | Industrial Connectors / Enclosures                      |
| Series           | <u>93601</u>                                            |
| Component Size   | 48B «104x62»                                            |
| Component Type   | Single Lever Hood                                       |
| IP Rating        | IP66                                                    |
| Overview         | <u>GWconnect Heavy Duty Connectors (HDC)</u>            |
| Product Category | Heavy Duty Connectors                                   |
| Product Name     | GWconnect                                               |
| Standard         | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type             | STD                                                     |
| UPC              | 887191836065                                            |

## Physical

|                     |                   |
|---------------------|-------------------|
| Hood Coating        | Polyester Powder  |
| Hood Color          | GREY RAL 7037     |
| Lock to Mating Part | Yes               |
| Material - Hood     | Die-cast Aluminum |
| Material - Peg      | Stainless Steel   |
| Number of Pegs      | 2                 |
| Packaging Type      | Bag               |
| Thread Size         | N/A               |
| Thread Type         | N/A               |

## Electrical

Voltage - Maximum 500V

## Material Info

Engineering Number 7848.7149.0



Series image - Reference only

## EU ELV

**Not Relevant**

## EU RoHS

## Compliant

## REACH SVHC

Not Contained Per -  
ED/71/2019 (16 July  
2019)

### Halogen-Free

## Status

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

### Search Parts in this Series

93601 Series

### Use With

Size 48B «104x62» S-D, S-DD, S-E, S-EP,  
S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4581