

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014684](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect STD - Standard, Single Lever Hood, Polyamide, with 2 Pegs, Top Entry, with Cable Gland, Size «32x13», Pg16 Thread, Black

Documents:

3D Model	3D Model (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Color - Cable Jacket	N/A
Component Size	«32X13»
Component Type	Single Lever Hood
IP Rating	IP66, IP67
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842615

Physical

Cable Diameter	8.00-14.00mm
Entry Location	Top
Flammability	UL 94V-0
Gland Color	Black RAL 9005
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Hood	Polyamide
Material - Peg	Polyamide
Net Weight	48.000/g
Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Electrical

Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number	7908.6646.1
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	936014684-000
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601](#) Series

Use With

Size «32x13» S-QD Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4684