

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936030074

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect Connector Kit, 16 Pole, Series S-E Female-Male Inserts, M25 Metal Cable Gland, M25 Die-cast Aluminum Hood-Side Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 16B «77x27», Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Kit components

Kit Components

[936000047](#) M25 Gland, [936012819](#) M25 Hood,
[936010273](#) Male Insert, [936010263](#) Female Insert,
[936012577](#) Vertical Bulkhead Housing

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93603</u>
Color - Cable Jacket	N/A
Component Size	16B «77X27»
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
UPC	887191864334

Physical

Lock to Mating Part	Yes
Mounting Style	Bulkhead
Net Weight	430.000/g
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	500V

Material Info

Engineering Number	7916.7751.5
--------------------	-------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
ED/71/2019 (16 July
2019)
lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93603 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93603-0074