

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936030078

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect Connector Kit, 16 Pole, Series S-E Female-Male Inserts, M25 Metal Cable Gland, M25 Die-cast Aluminum Hood-Side Entry, Surface Mount Housing-Vertical, 2 Lever, Size 16B «77x27». Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Kit components

Kit Components

936000047 M25 Gland, 936012819 M25 Hood,
936010273 Male Insert, 936010263 Female Insert,
936012561 SMT Vertical Housing

General

Product Family
Series
Color - Cable Jacket
Component Size
Component Type
Insert Series
Overview
Product Category
Product Name
UPC

Industrial Connectors / Enclosures
93603
 N/A
 16B «77X27»
 Connector Kit - Female+Male
 S-E
GWconnect Heavy Duty Connectors (HDC)
 Heavy Duty Connectors
 GWconnect
 887191864815

Physical

Lock to Mating Part
Mounting Style
Net Weight
Packaging Type
Thread Size
Thread Type

Yes
Surface Mount
630.000/g
Bag
M25
(M) Metric

Electrical

Current - Maximum per Contact
Voltage - Maximum

16.0A
500V

Material Info

Engineering Number

7916.7761.5



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
ED/71/2019 (16 July
2019)
lead

Halogen-Free Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93603 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93603-0078](#)