


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936030095](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Connector Kit, 24 Pole, Series S-E Female-Male Inserts, M25 Die-cast Aluminum Hood-Top Entry, Surface Mount Housing-Vertical, 2 Lever, Size 24B «104x27», Grey



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Kit components	
Kit Components	936012824 M25 Hood, 936010307 Male Insert, 936010297 Female Insert, 936013522 SMT Vertical Housing
General	
Product Family	Industrial Connectors / Enclosures
Series	93603
Component Size	24B «104X27»
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
UPC	887191865768
Physical	
Lock to Mating Part	Yes
Mounting Style	Surface Mount
Net Weight	790.200/g
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	500V
Material Info	
Engineering Number	7924.7767.0

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Contained Per - ED/71/2019 (16 July 2019) lead Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS
China ROHS ELV RoHS Phthalates	50 Image Not Relevant Not Contained

Search Parts in this Series
[93603](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93603-0095](#)