

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0956225881

Status:

Active

Overview:

Magnetic and Modular Jacks/Plugs

Description:

Modular Jack, Right-Angle, Surface Mount, 8/8, Shielded, Reel

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-95622-001-001 (PDF)


Packaging Specification PK-95122-002-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
UL		E107635
General		
Product Family		Modular Jacks/Plugs
Series		95622
Comments		Reflow Capable, External Shield
Component Type		PCB Jack
Magnetic		No
Overview		Magnetic and Modular Jacks/Plugs
Performance Category		3
Power over Ethernet (PoE)		N/A
Product Name		Modular Jack 8/8, RJ45
UPC		884982486638

Physical		
Boot Color		N/A
Color - Resin		Black
Durability (mating cycles max)		2500
Flammability		94V-0
Inverted / Top Latch		No
Jack Height		13.00mm
Keying to Mating Part		None
Lightpipes/LEDs		None
Material - Metal		Copper Alloy
Material - Plating Mating		Gold over Palladium Nickel
Material - Plating Termination		Tin
Material - Resin		High Temperature Thermoplastic
Net Weight		5.034/g
Orientation		Right Angle (Side Entry)
PCB Locator		No
PCB Retention		Yes
PCB Thickness - Recommended		1.57mm
Packaging Type		Embossed Tape on Reel
Pitch - Mating Interface		1.02mm
Pitch - Termination Interface		1.27mm
Plating min - Mating		0.051µm, 0.600µm
Plating min - Termination		1.905µm
Port Configuration		1x1
Positions / Loaded Contacts		8/8
Surface Mount Compatible (SMC)		Yes
Temperature Range - Operating		-40° to +85°C
Termination Interface: Style		Surface Mount
Waterproof / Dustproof		No
Wire/Cable Type		N/A



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

95622 Series

Mates With

95043 Modular Plug, Short Body

Electrical

Current - Maximum per Contact	1.5A
Grounding to PCB	Yes
Grounding to Panel	None
Shielded	Yes
Voltage - Maximum	125V DC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-95122-002-001
Product Specification	PS-95622-001-001
Sales Drawing	SD-95622-012-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[95622-5881](#)