

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0982660861](#)  
**Status:** **Active**  
**Overview:** [FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers](#)  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Tin (Sn) Plating, 17 Circuits

**Documents:**

|                                                                |                                                      |
|----------------------------------------------------------------|------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                                  | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">Product Specification PS-98266-001-001 (PDF)</a>   | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">Packaging Specification PK-98266-001-001 (PDF)</a> |                                                      |

**General**

|                         |                                                                           |
|-------------------------|---------------------------------------------------------------------------|
| Product Family          | Cable                                                                     |
| Series                  | <a href="#">98266</a>                                                     |
| Comments                | Contacts on the same side, Type A                                         |
| Crimp Quality Equipment | Yes                                                                       |
| Overview                | <a href="#">FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</a> |
| Product Name            | Premo-Flex FFC Jumper                                                     |
| UPC                     | 800756948539                                                              |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Length                  | 102.00mm        |
| Circuits (Loaded)             | 17              |
| Contact Layout Type           | A (same side)   |
| Material - Plating Mating     | Tin             |
| Packaging Type                | Bag             |
| Pitch - Mating Interface      | 0.50mm          |
| Temperature Range - Operating | -40° to +105°C  |
| Wire Size AWG                 | N/A             |
| Wire/Cable Type               | Flat Flex Cable |

**Electrical**

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A   |
| Voltage - Maximum             | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

|                         |                  |
|-------------------------|------------------|
| Packaging Specification | PK-98266-001-001 |
| Product Specification   | PS-98266-001-001 |
| Sales Drawing           | SD-98266-001     |



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**China RoHS**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[98266](#) Series

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[527451733](#) , [527461733](#) , [525591733](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98266-0861](#)