

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0982661083
Status: Active
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 127.00mm Cable Length, Tin (Sn) Plating, 37 Circuits

Documents:

- Drawing (PDF)
- Product Specification PS-98266-001-001 (PDF)
- Packaging Specification PK-98266-001-001 (PDF)
- Datasheet (PDF)
- RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Crimp Quality Equipment

Overview

Cable

98266

Contacts on the same side, Type A

Yes

FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Product Name

UPC

Premo-Flex FFC Jumper

800756940151

Physical

Cable Length

Circuits (Loaded)

Contact Layout Type

Material - Plating Mating

Packaging Type

Pitch - Mating Interface

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

127.00mm

37

A (same side)

Tin

Bag

0.50mm

-40° to +105°C

N/A

Flat Flex Cable

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-98266-001-001

PS-98266-001-001

SD-98266-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Not Reviewed

Not Reviewed

Not Reviewed

Search Parts in this Series

98266 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

98266-1083