

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0982761003

Status:

Active

Overview:

NSCC - New Standard Casing Contact

Description:

3.33mm / 6.00mm Pitch Hybrid Male Inline Housing, Dual Row, 16 Circuits, Blue

Documents:

3D Model

Packaging Specification PK-98276-001-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Application Specification AS-98276-001-001 (PDF)

General	
Product Family	Crimp Housings
Series	98276
Application	Power, Wire-to-Wire
Comments	For current designation please refer to FCI Sicma terminal specification for 1.50 and 2.80mm terminals.
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348213191
Physical	
Circuits (maximum)	16
Circuits Detail	4x2.8mm 12x1.5mm male terminals
Color - Resin	Natural, Natural (White)
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Polyester, Polyester Alloy
Net Weight	12.361/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.33mm, 6.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +85°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-98276-001-001
Packaging Specification	PK-98276-001-001
Sales Drawing	SD-98276-001-001



Series image - Reference only

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

98276 Series

Mates With

982731003

Use With

1.5 and 2.8mm FCI Sicma Male Terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98276-1003](#)