

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0987841001

Status:

Active

Overview:

NSCC - New Standard Casing Contact

Description:

NSCC Receptacle Connector 3.33mm Pitch, 1.50mm, Shorting Bar, Long, 5 Circuits, Black

Documents:

3D Model

Application Specification AS-98784-005-CH-001 (PDF)

Drawing (PDF)

Packaging Specification PK-98784-001-001 (PDF)

Application Specification AS-98784-005-001 (PDF)

RoHS Certificate of Compliance (PDF)

|                                    |                                       |
|------------------------------------|---------------------------------------|
| <b>General</b>                     |                                       |
| Product Family                     | Crimp Housings                        |
| Series                             | 98784                                 |
| Application                        | Wire-to-Wire                          |
| Overview                           | NSCC - New Standard Casing Contact    |
| Product Name                       | NSCC                                  |
| UPC                                | 822350574051                          |
| <b>Physical</b>                    |                                       |
| Circuits (maximum)                 | 5                                     |
| Circuits Detail                    | 5                                     |
| Color - Resin                      | Black                                 |
| Gender                             | Receptacle                            |
| Glow-Wire Capable                  | No                                    |
| Lock to Mating Part                | Yes                                   |
| Material - Resin                   | PBT                                   |
| Net Weight                         | 4.920/g                               |
| Number of Rows                     | 1                                     |
| Packaging Type                     | Carton                                |
| Panel Mount                        | No                                    |
| Pitch - Mating Interface           | 3.33mm                                |
| Polarized to Mating Part           | Yes                                   |
| Stackable                          | No                                    |
| Temperature Range - Operating      | -40° to +85°C                         |
| <b>Solder Process Data</b>         |                                       |
| Lead-freeProcess Capability        | N/A                                   |
| <b>Material Info</b>               |                                       |
| <b>Reference - Drawing Numbers</b> |                                       |
| Application Specification          | AS-98784-005-001, AS-98784-005-CH-001 |
| Packaging Specification            | PK-98784-001-001                      |
| Sales Drawing                      | SD-98784-001                          |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Not Relevant

Compliant

Not Contained

Search Parts in this Series

98784 Series

Mates With

987811001 NSCC 3.33mm Pitch Long Version Male Housing

Use With

98897 NSCC Receptacle Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98784-1001](#)