

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0988171021

Status:


Active

Overview:

NSCC - New Standard Casing Contact

Description:

NSCC Single Part, Unsealed, 1.50mm, Female Housing, 3.33mm Pitch NSCC, Wire-to-Wire, 2 Circuits, Black



Documents:	
3D Model	Application Specification 988210001-PS-CH-001 (PDF)
Drawing (PDF)	Application Specification AS-98821-001-001 (PDF)
Product Specification PS-98821-001-001 (PDF)	Packaging Specification PK-31301-635-001 (PDF)
Application Specification 988210001-AS-CH-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link	
Application Tooling Part Link	63813-3800
General	
Product Family	Crimp Housings
Series	98817
Application	Power, Wire-to-Wire
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348761357
Physical	
Breakaway	No
Circuits (maximum)	2
Circuits Detail	2 x 1.5mm female terminals
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.640/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	3.33mm
Pitch - Termination Interface	3.33mm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	10.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	010009321
Reference - Drawing Numbers	
Application Specification	988210001-AS-CH-001, 988210001-PS-CH-001, AS-98821-001-001
Packaging Specification	PK-31301-635-001

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

98817 Series

Mates With

988221021 Male Receptacle Housing

Use With

Female Terminal NSCC 988971109 , 988971119 , 988971129 or FCI Female Terminal 1.5 Sicma 3

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extractor Tool for

Unsealed Receptacle Connectors

638133800

This document was generated on 01/25/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98817-1021](#)