

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0988231016](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: NSCC Male Housing, Terminal Size 1.50mm, Non-Sealed, 5.0mm Pitch, 10 Circuits, Blue

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Application Specification AS-98816-001-001 \(PDF\)](#)
[Packaging Specification PK-31301-635-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Housings
Series	98823
Application	Power, Wire-to-Wire
Comments	Pitch Center Spacing: Horizontal Pitch 3.33mm, Vertical pitch 6.00mm
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348801114
Physical	
Circuits (maximum)	10
Circuits Detail	10x1.5mm pins
Color - Resin	Blue
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	8.000/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.33mm, 6.00mm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	10.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	08116EV10F6
Reference - Drawing Numbers	
Application Specification	AS-98816-001-001
Packaging Specification	PK-31301-635-001
Sales Drawing	SD-98823-001



Series image - Reference only

EU ELV Compliant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)4578-DC (25 June 2020) Halogen-Free Status Not Relevant	China RoHS
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[98823](#) Series

Mates With
[988161016](#) , [988161116](#) (Female
Receptacle Housing)

Use With
Use: Male FCI Terminals

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98823-1016](#)