

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0988981029](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: 5.00mm Pitch UCC2 Receptacle Terminal, 0.35mm²; to 0.75mm²;(AWG 20-22), Reel, Pre Tin Plated

Documents:

3D Model	Application Specification AS-98898-001-001 (PDF)
Drawing (PDF)	Application Specification AS-98906-001-001 (PDF)
Product Specification PS-98821-001-001 (PDF)	Packaging Specification 313025040-000 (PDF)
Application Specification 988210001-AS-CH-001 (PDF)	Packaging Specification PK-98898-002-001 (PDF)
Application Specification 988210001-PS-CH-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-98821-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	98898
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348815678

Physical

Gender	Female
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.737/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.35-0.75mm
Wire Size AWG	20, 22
Wire Size mm ²	0.35-0.75

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2120509CA201H
--------------------	---------------

Reference - Drawing Numbers

Application Specification	988210001-AS-CH-001, 988210001-PS-CH-001, AS-98821-001-001, AS-98898-001-001, AS-98906-001-001
Packaging Specification	313025040-000, PK-98898-002-001
Product Specification	PS-98821-001-001
Sales Drawing	SD-98898-100-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[98898](#) Series

Use With

NSCC Receptacle Connector [98819](#) , [98821](#) , [98273](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 2.80mm Pitch UCC2 Receptacle Terminal	638230400
FineAdjust Applicator for 2.8 UCC2 Receptacle Terminal	639015700

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

98898-1029