

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1054051316

Status:

Active

Overview:

Nano-Fit Power Connectors

Description:

Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Dual Row, 16 Circuits, 0.76µm Gold (Au) Plating, Black, Glow-Wire Capable

- Documents:
- 3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification 1054051000-PS-CH-000 (PDF)

Product Specification 1054051000-PS-ES-000 (PDF)

Product Specification 1054051000-PS-SK-000 (PDF)

Product Specification PS-105405-001-001 (PDF)

Application Specification AS-105405-001-001 (PDF)

Packaging Specification PK-105405-004-000 (PDF)

Test Summary 1054050000-TS-000 (PDF)

Datasheet (PDF)

Symbol Footprint Data SYM-105405-XX16-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	105405
Application	Power, Wire-to-Board
Overview	Nano-Fit Power Connectors
Product Name	Nano-Fit
UPC	889056259897

Physical	
Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	50
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	1.960/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Temperature Range - Operating	-40° to +115°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	250V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

105405 Series

Mates With

Nano-Fit Receptacle Housing 1053081216

Material Info

Reference - Drawing Numbers

Application Specification	AS-105405-001-001
Packaging Specification	PK-105405-004-000
Product Specification	1054051000-PS-CH-000, 1054051000-PS-ES-000, 1054051000-PS-SK-000, PS-105405-001-001
Sales Drawing	SD-105405-001-000
Symbol/Footprint Data	SYM-105405-XX16-001
Test Summary	1054050000-TS-000

This document was generated on 09/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[105405-1316](#)