

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1060051001](#)
Status: **Active**
Overview: [Optical Connectivity Solutions](#)
Description: MPO Loopback, Multimode, 12 Fiber, 50/125µm, Standard Pin Out

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Fiber Optic Assemblies
Series	106005
Boot Type	N/A
Connector to Connector	N/A
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Name	MPO
UPC	800756925349
Physical	
Cable Length	LOOPBACK
Cable Size	50/125µm
Fiber (Core/Cladding)	50/125µm
Net Weight	95.270/g
Single Ended	Yes
Wire/Cable Type	Ribbon Cable

Material Info

Reference - Drawing Numbers	
Sales Drawing	SD-106005-1000-001



EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
[106005](#) Series

Mates With
MTP Adapter [106181](#) , [106114](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

106005-1001