

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1060597100

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

Optical Industrial Plug Assembly, Metal Body, Outdoor Cable, LC, Multimode Male with Logo



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Fiber Optic Connectors
Series	106059
Cable Size	8.00mm max.
Material - Housing	PEI
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Name	LC
UPC	822350957229
Wire/Cable Type	Round
Physical	
Alignment Sleeve	Metal
Angled Physical Contact (APC)	No
Boot Color	N/A
Boot Type	N/A
Color - Resin	METAL
Ferrule Hole Size	127µm
Ferrule Material	Ceramic
Gender	Male
Mounting Style	Adhesive
Net Weight	107.590/g
Ports	2
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-106059-7100-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

106059 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106059-7100](#)