

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1060598008

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

Optical Industrial Plug Connector, Metal Body, LC, Single Mode



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	Fiber Optic Connectors
Series	106059
Cable Size	8.00mm max.
Material - Housing	Metal
Mode	Singlemode
Overview	Optical Connectivity Solutions
Product Name	Industrial LC
UPC	887191168272
Wire/Cable Type	Fiber Optic - 2 Fiber
Physical	
Alignment Sleeve	N/A
Angled Physical Contact (APC)	No
Boot Color	N/A
Boot Type	N/A
Color - Resin	METAL
Ferrule Hole Size	125.5µm
Ferrule Material	Ceramic
Gender	Plug
Mounting Style	Bayonet
Net Weight	33.900/g
Ports	2
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-106059-8000-001

EU ELV
Not Relevant

EU RoHS
Compliant with
Exemption 6(b),6(c)
REACH SVHC
Contained Per -
D(2021)4569-DC (8
July 2021)
Lead
Halogen-Free
Status
Not Low-Halogen

China RoHS

50 Image
Not Relevant
Not Contained

For more information, please visit [Contact US](#)

Search Parts in this Series

106059 Series

Mates With

Fiber Optic Adapters 106059 , 106501

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

106059-8008