

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1062250012

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

MPO Female-to-MPO Female Trunk Cable Assembly, 9/125µm, 4.80mm, Singlemode, 12 Fiber, Plenum, OS2, 100.0m Length, Yellow



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Fiber Optic Assemblies
Series	106225
Boot Type	Straight
Connector to Connector	MPO-to-MPO
Mode	Singlemode
Overview	Optical Connectivity Solutions
Product Name	MPO
UPC	191128250245
Physical	
Cable Length	100.0m
Cable Size	4.80mm
Fiber (Core/Cladding)	9/125µm
Net Weight	2173.653/g
Single Ended	No
Wire/Cable Type	12 Fiber OS2 Plenum
Material Info	
Reference - Drawing Numbers	
Sales Drawing	1062250000-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

106225 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106225-0012](#)