


TRUNK CABLE P/N	OVERALL LENGTH, L (m)	CABLE TYPE	FIBER TYPE	CONNECTOR/ CABLE COLOR	INSERTION LOSS	RETURN LOSS
1062250061	1.0 +0.2 / -0	SINGLE JACKET	MM 50/125 μm OM3 BIF	AQUA / AQUA	0.5 dB @ 850 nm	---
1062250062	3.0 +0.2 / -0					
1062250063	5.0 +0.2 / -0					
1062250013	10.0 +0.2 / -0					
1062250064	15.0 +0.3 / -0	RUGGEDIZED DUAL JACKET				
1062250014	25.0 +0.5 / -0					
1062250015	50.0 +1.0 / -0					
1062250016	100.0 +2.0 / -0					
1062250065	1.0 +0.2 / -0	SINGLE JACKET	MM 50/125 μm OM4 BIF			
1062250066	3.0 +0.2 / -0					
1062250067	5.0 +0.2 / -0					
1062250017	10.0 +0.2 / -0					
1062250068	15.0 +0.3 / -0	RUGGEDIZED DUAL JACKET				
1062250018	25.0 +0.5 / -0					
1062250019	50.0 +1.0 / -0					
1062250020	100.0 +2.0 / -0					
1062250069	1.0 +0.2 / -0	SINGLE JACKET	SM 9/125 μm OS2 ITU-T G.657.A1 BIF	YELLOW / YELLOW	0.5 dB @ 1550 nm	- 50 dB @ 1550 nm
1062250070	3.0 +0.2 / -0					
1062250071	5.0 +0.2 / -0					
1062250021	10.0 +0.2 / -0					
1062250072	15.0 +0.3 / -0	RUGGEDIZED DUAL JACKET				
1062250022	25.0 +0.5 / -0					
1062250023	50.0 +1.0 / -0					
1062250024	100.0 +2.0 / -0					

CONNECTIONS	
FROM	TO
P1-1 THRU P1-12	P2-13 THRU P2-24
P1-13 THRU P1-24	P2-1 THRU P2-12



NOTES:

- ENDCAPS ARE NOT SHOWN BUT INLCUED.
- LABEL IS PRINTED WITH MOLEX P/N AND SERIAL NUMBER.
- FOR DETAILED PRODUCT SPECIFICATION SEE DOCUMENT 1062250000 ES.
- CABLE CONSTRUCTION:
 - L < 25 meters - SINGLE JACKET CABLE
 - L ≥ 25 meters - RUGGEDIZED CENTRAL TUBE CABLE
- INSERTION LOSS TEST DATA IS PROVIDED WITH EACH SHIPMENT.
- PACKAGING:
 - L < 50 meters - INDIVIDUALLY COILED AND BAGGED
 - L ≥ 50 meters - SHIPPED ON SPOOLS

VIEW A
SCALE 5:1

VIEW B
SCALE 5:1

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
= 0	EC NO: 2019/01/03 DRWN: IGUMIN CHKD: GGENCHANOK REV: 2019/01/03	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE							
= 0			mm	1:1								
= 0			DRWN BY		DATE							
= 0			CHK'D BY		DATE							
= 0			ANGULAR TOL ± °		APPR BY		DATE		PRODUCT CUSTOMER DRAWING			
= 0			4 PLACES ±		IGUMIN		2017/02/16					
= 0	3 PLACES ±		CHK'D BY		DATE		SERIES: 106225 MATERIAL NUMBER: SEE TABLE CUSTOMER: 1062250013					
= 0	2 PLACES ±		APPR BY		DATE							
= 0	1 PLACE ±		IGUMIN		2017/03/21		DOCUMENT NUMBER: 1062250013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 1 OF 1					
= 0	0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION							
= 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		D									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106225-0018](#)