

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1065018004](#)
Status: **Active**
Overview: [Optical Connectivity Solutions](#)
Description: Industrial ODVA SFP Receptacle, Flange Mount, with Plastic Dust Cover

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Fiber Optic Adapters
Series [106501](#)
Component Type Receptacle
Mode Singlemode and Multimode
Overview [Optical Connectivity Solutions](#)
Product Name Industrial, ODVA SFP Receptacle
Type Adapter
UPC 889056220828

Physical
Alignment Sleeve N/A
Angled Physical Contact (APC) No
Color - Resin N/A
Ferrule Material Ceramic
Gender Receptacle
Material - Housing Nickel Plated Zinc Alloy
Mounting Style Bayonet
Net Weight 50.200/g
Orientation Straight
Panel Mount With Flange
Ports 1
Shutter No

Electrical
Shield Type N/A
Shielded No

Material Info

Reference - Drawing Numbers
Sales Drawing SD-106501-8004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[106501](#) Series

Mates With

Plug Connectors [106059](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106501-8004](#)