

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1110192020

Status:

Active

Overview:

HSAutoLink Interconnect Systems

Description:

HSAutoLink Cable Assembly, LVDS MINI-B Plug-to-MINI-B Inline Receptacle, 0.50m Length, Polarization A-to-B



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	111019
Application	Automotive
Assembly Configuration	Dual Ended Connectors
Connector to Connector	STP 100/PG Mini-B-to-Mini-B
Overview	HSAutoLink Interconnect Systems
Product Name	HSAutoLink LVDS
UPC	883906510275
Physical	
Cable Length	0.50m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	34.400/g
Number of Rows	1
Single Ended	No
Wire/Cable Type	Round
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-111019-2000-001

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

111019 Series

Mates With

49616 USCAR/USB Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[111019-2020](#)