

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1110683202](#)
Status: **Active**
Overview: [iPass+ HD Interconnect System](#)
Description: [iPass X4 Mini SAS HD-to-Mini SAS 2.0, 2.0m, 28 AWG](#)

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 1110750001-000 \(PDF\)](#)

General
Product Family Cable Assemblies
Series [111068](#)
Assembly Configuration Dual Ended Connectors
Connector to Connector iPass HD-to-Mini SAS
Overview [iPass+ HD Interconnect System](#)
Product Name iPass, X4
UPC 884982770713

Physical
Cable Length 2.0m
Circuits (Loaded) 36
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Zinc Alloy
Material - Plating Mating Gold
Net Weight 220.300/g
Single Ended No
Waterproof / Dustproof No
Wire Insulation Diameter N/A
Wire Size AWG 28
Wire/Cable Type Parallel Pair

Electrical
Impedance 100Ω
Shielded Yes

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Application Specification 1110750001-000
Sales Drawing SD-111068-3200



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Contained Per -
ED/88/2018 (15
January 2019)
2,4-Di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p

Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[111068](#) Series

Mates With
HD Plug Mates to 1x1, 1x2 and x4
Receptacle - EMI Housing [46866](#). Mini-SAS
Plug mates to Receptacle [755860004](#) and
EMI Housing [4548](#)>BR>

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

111068-3202