

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120110024

Status:


Active

Overview:

PC Network Interface Cards

Description:

SST PB3 Card, PROFIBUS DP Master/Slave, 1 Channel, PCI 3.3/ 5V -DLL/LIB - Control - Bulk of 25



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Network Interface
Series	112011
Application	IO Control
Approvals	CE certified
Comments	1 channel
Overview	PC Network Interface Cards
Product Name	SST
Protocol	PROFIBUS
Protocol Detail	PROFIBUS DPV0 Master, PROFIBUS DPV0 Slave, PROFIBUS DPV1 Master
Software Downloads	
Type	SST-PB3-PCU
UPC	PROFIBUS Card 78678801838
Physical	
Channels	1
Communication Speed	PROFIBUS 9.6 kbps to 12 Mbps
Interface	CommDTM, DLL, OPC DA
Mounting Style	PC Slot
Net Weight	140.000/g
Network Connection Type	PROFIBUS D-Sub Female (9 pin)
Operating System	Windows7, Windows8/8.1, Windows Server 2003, Windows Server 2008, Windows Server 2012, Windows Vista, WindowsXP
Packaging Type	
Processor	Carton
Slot	ColdFIRE 5272
Temperature Range - Operating	Universal PCI 3.3V/5V 0°C to +60°C
Electrical	
EMC	EN 61000-3-2, EN 61000-3-3, IEC 61000-6-2
Supply Voltage	3.3/5V
Material Info	
Engineering Number	SST-PB3-PCU-B25
Reference - Drawing Numbers	
Sales Drawing	SD-112011-0009

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112011 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1120110024