

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120361003

Status:

Active

Overview:

Industrial Ethernet Switches

Description:

IP20 Unmanaged Ethernet Switch, 8 Ports, 10/100/1000Mb Data Speed



Documents:	
Datasheet (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	Switches
Series	112036
Approvals	CE, FCC, UL (pending)
Comments	10/100/1000 Base TX (Mbaud)
Data Speed	Gigabit (10/100/1000Mbps)
IP Rating	IP20
MAC Address	8192
Overview	Industrial Ethernet Switches
Product Name	IP20 Unmanaged Ethernet Switch
Protocol	N/A
Switch Functionality	Unmanaged
UPC	78172561266
Physical	
Ethernet Connector	RJ45
Housing Depth	99.60mm
Housing Length	116.00mm
Housing Width	46.00mm
Mechanical Shock	IEC 60068-2-27
Mounting Style	DIN Rail, Wall
Packaging Type	Carton
Ports	8
Power Input	24V DC
Temperature Range - Operating	-40° to +70°C
Uplink Connection	N/A
Vibration	IEC 60068-2-6
Electrical	
Current - Maximum Output	N/A
EMC	CE, EN 610006-2-4, FCC Part 15, ICES-003
Supply Voltage	24V DC
Material Info	
Engineering Number	DRL-280MG

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

112036 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[112036-1003](#)