

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120385005

Status:

Active

Overview:

IP67-Rated HarshIO Modules

Description:

Brad HarshIO Digital Module for PROFIBUS, Classic 60mm, IP67, 8 Ports M12, 16 Univ. & User conf. Input/Output, 5 Pole Power

Documents:

Drawing (PDF)

Product Literature (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial I/O Modules
Series	112038
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	PI, UL, cUL, CE
Comments	Universal & User Configurable input / output channels., Universal & User Configurable input / output channels.
EPLAN	Yes
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Literature Order No	987650-5701
Product Name	HarshIO PROFIBUS DP
Protocol	PROFIBUS DP
Software Downloads	TCDPB-8xxx-xxx
UPC	884982299122
Physical	
Bus Input	5-pole Micro-Change (M12), B-Coded, Male
Bus Output	5-pole Micro-Change (M12), B-Coded, Female
Format	Classic (60mm)
Housing Width	60.00mm
I/O Connector	5-pole Micro-Change (M12), A-Coded, Female
I/O Ports	8x M12
I/O Signal Mix	16 Input / Output Configurable
Mechanical Shock	10G, 11ms, 3 AXIS
Net Weight	616.000/g
Power Input	5-pole Mini-Change, Male
Power Output	5-pole Mini-Change, Female
Temperature Range - Operating	-25°C to +70°C
Vibration	IEC 60068-2-6
Electrical	
Current - Maximum Output	2.0A per Channel
EMC	IEC 61000-6-2
Input Delay	2.5ms
Input Device Supply	140 mA per port at 25°C
Input Type	Configurable
Material Info	
Engineering Number	TCDPB-8YYY-B1U
Reference - Drawing Numbers	
Sales Drawing	1120380030-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112038 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1120385005](#)