

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120955122

Status:

Active

Overview:

IP67-Rated HarshIO Modules

Description:

Brad HarshIO Ethernet/IP IO-Link Module, IP67, 8 Ports M12, 8 IO-Link / 8 Digital IO
User Configurable, PNP, 4 Pole Power



Documents:	
3D Model	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	Product Literature (PDF)
Drawing (PDF)	

General	
Product Family	Industrial I/O Modules
Series	112095
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	CE, UL, cUL
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Name	HarshIO EtherNet/IP
Protocol	EtherNet/IP, IO-Link
Software Downloads	TCIEI-888P-DxU
UPC	889056236386
Physical	
Bus Input	4-pole Ultra-Lock (M12), D-Coded, Female
Bus Output	4-pole Ultra-Lock (M12), D-Coded, Female
Format	Classic (60mm)
Housing Width	60.00mm
I/O Connector	5-pole Ultra-Lock (M12), A-Coded, Female
I/O Ports	8x M12
I/O Signal Mix	8 IO configurable / 8 IO-Link
Mechanical Shock	EN 60068-2-6, EN 60068-2-29
Net Weight	620.000/g
Power Input	4-pole Mini-Change, Male
Power Output	4-pole Mini-Change, Female
Temperature Range - Operating	-25°C to +70°C
Vibration	EN 60068-2-29, EN 60068-2-6
Electrical	
Current - Maximum Output	2.0A per Channel
EMC	EN 61000-6-2, EN 61000-6-4
Input Delay	0,1,3 or 5 ms
Input Device Supply	1.6A per port at 25°C
Input Type	PNP or Dry Contact
Material Info	
Engineering Number	TCIEI-888P-DYU
Reference - Drawing Numbers	
Sales Drawing	1120955119-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112095 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[112095-5122](#)