

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1120955127](#)
Status: **Active**
Overview: [IP67-Rated HarshIO Modules](#)
Description: Brad EtherNet/IP CIP Safety HarshIO Modules, Classic 60.00mm, IP67, 8 Ports M12, 12 PNP Safety Inputs, 4 Sourcing Safety Outputs, M8 Memory Key, 4-Pole Power

Documents:

3D Model	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	

General

Product Family	Industrial I/O Modules
Series	112095
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	CE, UL, cUL, TÜV, ODVA
Comments	12 safe inputs + 4 safe outputs, Cat 4 / PLe, M8 memory key
EPLAN	Yes
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Name	HarshIO EtherNet/IP, IP CIP Safety
Protocol	EtherNet/IP CIP Safety
Software Downloads	TCDEC-8B4x-DxU-Gx
UPC	889056265188

Physical

Bus Input	4-pole Micro-Change (M12), D-Coded, Female
Bus Output	4-pole Ultra-Lock (M12), D-Coded, Female
Format	Classic (60mm)
Housing Width	60.00mm
I/O Connector	5-pole Ultra-Lock (M12), A-Coded, Female
I/O Ports	8x M12
I/O Signal Mix	12 input / 4 output
Mechanical Shock	15G, 11ms, 3 AXIS
Net Weight	1054.148/g
Power Input	4-pole Mini-Change
Power Output	4-pole Mini-Change
Temperature Range - Operating	-25°C to +70°C
Vibration	50G, 6ms, 3 AXIS

Electrical

Current - Maximum Output	1.0A per Channel
EMC	EN 62061:2005+AC:2010+A1:2013, IEC 61131-2:2007
Input Delay	ON – OFF, OFF – ON
Input Device Supply	700mA per port
Input Type	PNP or Dry Contact

Material Info

Engineering Number	TCDEC-8B4P-DYU-G8
--------------------	-------------------

Reference - Drawing Numbers

Sales Drawing	1120955087-000
---------------	----------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[112095](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1120955127](#)