

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120955138

Status:

Active

Overview:

IP67-Rated HarshIO Modules

Description:

Brad HarshIO Digital Module for EtherNet/IP, Classic 60mm, IP67, 8 ports M12, 8 Inputs / 8 Outputs, PNP, 4 Pole Power, 3 Rotary Switch

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E200650
General	
Product Family	Industrial I/O Modules
Series	112095
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	ODVA, UL, cUL, CE
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Name	HarshIO EtherNet/IP
Protocol	EtherNet/IP
Software Downloads	TCDEI-8xxP-DxU-G02
UPC	889056361903
Physical	
Bus Input	4-pole Ultra-Lock (M12), D-Coded, Female
Bus Output	4-pole Ultra-Lock (M12), D-Coded, Female
Format	Classic (60mm)
Housing Width	60.00mm
I/O Connector	5-pole Ultra-Lock (M12), A-Coded, Female
I/O Ports	8x M12
I/O Signal Mix	8 input / 8 output
Mechanical Shock	10G, 11ms, 3 AXIS
Net Weight	595.000/g
Power Input	4-pole Mini-Change, Male
Power Output	4-pole Mini-Change, Female
Temperature Range - Operating	-25°C to +70°C
Vibration	IEC 60068-2-6
Electrical	
Current - Maximum Output	2.0A per Channel
EMC	IEC 61000-6-2
Input Delay	5 ms
Input Device Supply	140 mA per port at 25°C
Input Type	PNP or Dry Contact
Material Info	
Engineering Number	TCDEI-888P-DYU-G02
Reference - Drawing Numbers	
Sales Drawing	1120955011-000



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112095 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

112095-5138