

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1121055006

Status:

Active

Overview:

Industrial Ethernet Switches

Description:

Direct-Link Industrial 8-Port, IP67 (Machine Mount) Ethernet Switch, Unmanaged, M12 Ultra-Lock, 10/100 Mb/s

Documents:

Drawing (PDF)

Product Literature (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Approvals

Comments

IP Rating

MAC Address

Overview

Product Name

Protocol

Switch Functionality

UPC

Switches

112105

CE certified, UL (pending)

2.4W (24VDC), 2.4W (24VDC)

IP67

N/A

Industrial Ethernet Switches

Direct-Link

EtherNet (IEEE 802.3)

Unmanaged

887191685229

Physical

Ethernet Connector

Housing Width

Mechanical Shock

Mounting Style

Packaging Type

Ports

Power Input

Temperature Range - Operating

Uplink Connection

Vibration

4-Pole Ultra-Lock® (M12) Conn

60.00mm

50G (IEC 68-2-29)

N/A

Carton

8

5-pole Micro-Change (M12)

-40° to +75°C

5-Pole Micro-Change (M12)

7g (IEC 68-2-29)

Electrical

Current - Maximum Output

EMC

Supply Voltage

N/A

EN 61000-4-2, EN 61000-4-4, EN 61000-4-5, EN 61326

2.4W (24V DC)

Material Info

Engineering Number

DRL-782

Reference - Drawing Numbers

Sales Drawing

1121055006-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

112105 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1121055006