

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200060562](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 0.34mm² Black PVC Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
Series [120006](#)
Connector End A Micro-Change (M12)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name Micro-Change (M12)
Protocol N/A
Region Europe
Type Single Ended
UPC 883906068004

Physical

Cable Diameter 5.40mm (.213")
Cable Length 5.0m (16.40')
Color - Cable Jacket Black
Coupling Style Threaded
Gender Male-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Net Weight 244.270/g
Orientation Straight to Pigtail
Poles 4
Temperature Range - Operating -30° TO +80°C
Wire Size AWG 22
Wire/Cable Type UL 2464

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 60V

Material Info

Engineering Number 804006E03M050

Reference - Drawing Numbers

Sales Drawing 1200659185-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000380967_00_000.pdf

Search Parts in this Series

[120006 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200060562](#)