

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200070472

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 0.34mm² PVC Cable, 0.60m (1.97') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Industrial Cordsets

Series

120007

Connector End A

Micro-Change (M12)

Connector End B

Micro-Change (M12)

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Micro-Change (M12) Connectors

Product Name

Micro-Change (M12)

Protocol

N/A

Region

Europe

Type

Double Ended

UPC

883906073534

Physical

Cable Diameter

5.40mm (.213")

Cable Length

0.60m (1.97')

Color - Cable Jacket

Black

Coupling Style

Threaded

Gender

Female-Male

Keyway

Single

LED Indicator

No

Material - Cable Jacket

PVC

Material - Connector Body

PUR

Material - Coupling Nut

Nickel-plated Brass

Material - O-Ring

Fluoro-elastomer

Material - Plating Mating

Gold

Net Weight

40.483/g

Orientation

Straight to Straight

Poles

4

Temperature Range - Operating

-30°C TO +80°C

Wire Size AWG

22

Wire/Cable Type

UL 2464

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

60V

Material Info

Engineering Number

884030E03M006

Reference - Drawing Numbers

Sales Drawing

1200668084-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120007 Series

This document was generated on 10/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200070472