

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200310028

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Receptacle, 5 Poles, M8 x 0.5 Mounting Threads, Female (Straight) to 22 AWG Leads, 0.30m (11.81") Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E152210
General	
Product Family	Industrial Receptacles
Series	120031
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	883906177850
Physical	
Coupling Type	Internal Thread
Gender	Female
Keyway	B-coded
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 0.5
Net Weight	652.000/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-25° to +90°C
Wire Size AWG	24
Wire/Cable Type	UL 1569
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	4R5F30E02C3003
Reference - Drawing Numbers	
Sales Drawing	4RXF30XXXXXXX3-001, SD-120090-028-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free Status

Not Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120031 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200310028