

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200650048

Status:

Active

Overview:

Brad Micro-Push M12 Cordsets and Connectors

Description:

Micro-Push (M12) Single-Ended Cordset, 3 Poles, Female (Straight)-to-Pigtail, 22 AWG, Unshielded PVC Cable, 2.0m (6.56') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Push (M12)
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Copper Alloy
Overview	Brad Micro-Push M12 Cordsets and Connectors
Product Name	Micro-Push
Protocol	N/A
Type	Single Ended
UPC	78678850597
Physical	
Cable Diameter	4.70mm (.185")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-25°C to +105°C
Wire Size AWG	22
Wire/Cable Type	Unshielded PVC
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	N03000A41M020G
Reference - Drawing Numbers	
Sales Drawing	SD-120065-084-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Not Relevant

Compliant

Not Contained

Search Parts in this Series

120065 Series

Mates With

Micro-Change M12 Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120065-0048