

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200651422](#)
Status: **Active**
Overview: [Brad Micro-Push M12 Cordsets and Connectors](#)
Description: Micro-Push (M12) Single-Ended Cordset, 3 Poles, Female (90°)-to-Pigtail, 22 AWG, Unshielded PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
Series [120065](#)
Connector End A Micro-Push (M12)
Connector End B Pigtail
IP Rating IP65
Material - Contact Copper Alloy
Overview [Brad Micro-Push M12 Cordsets and Connectors](#)
Product Name Micro-Push
Protocol N/A
Type Single Ended
UPC 78678851096

Physical

Cable Diameter 4.70mm (.185")
Cable Length 2.0m (6.56')
Color - Cable Jacket Black
Coupling Style Push to Lock
Gender Female-Pigtail
Keyway A-coded
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body Nylon
Material - Coupling Nut N/A
Material - Plating Mating Gold
Orientation 90° to Pigtail
Poles 3
Temperature Range - Operating -25°C to +105°C
Wire Size AWG 22
Wire/Cable Type Unshielded PVC

Electrical


Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number N03001A41M020G

Reference - Drawing Numbers

Sales Drawing SD-120065-085



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[120065](#) Series

Mates With

Micro-Change M12 Connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120065-1422](#)