


10 9 8 7 6 5 4 3 2 120065

MATERIAL NO.	ENGINEERING NO.	FINISHED LENGTH
1200652213	804000A14M010A	3' 4" +2.19-0 (1M +55.6mm-0)
1200652223	804000A14M020A	6' 7" +3.50-0 (2M +88.9mm-0)
1200652224	804000A14M030A	9' 10" +3.50-0 (3M +88.9mm-0)
1200652220	804000A14M050A	16' 5" +6.50-0 (5M +165.1mm-0)
1200652225	804000A14M100A	32'10" +12.50-0 (10M +317.5mm-0)

CUSTOMER PRODUCTION APPROVAL
APPROVED BY: _____
DATE: _____
MUST BE SIGNED AND RETURNED BEFORE
PRODUCTION WILL BEGIN.

RESTRICTED SALES DRAWING



FEMALE FACE VIEW
SCALE: 2X

S1	BROWN
1	WHITE
2	BLUE
3	BLACK

WIRING DIAGRAM

NOTES:
 1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. ELECTRICAL SPECIFICATIONS
 VOLTAGE RATING: 250V AC/DC
 CURRENT RATING: 4 AMPS
 4. PROTECTION: IP67
 5. ASSEMBLY IS RoHS COMPLIANT
 BY EXEMPTION

WRAP LABEL			VINYL	BLACK/YELLOW	RELEASED AS SD DOC 120065-10 EC NO.: PG2013-1269	DRAWN BY RSTONE 2013/02/12	CHECKED BY K JOZWIK 2013/02/27	APPROVED BY JFMURPHY 2013/06/21	DIMENSION STYLE IN/MM	SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH					QUALITY SYMBOLS ▼=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	REV	
7	1	OVERMOLD-FEMALE	PVC	GRAY					4 PLACES	± ---	± ---	
6	1	O-RING	VITON	RED					3 PLACES	± ---	± ---	
5	1	COUPLING, FEMALE THREAD	BRASS	NICKEL PLATED					2 PLACES	± ---	± .01	
4	1	CONTACT SOCKET	Cu ALLOY	GOLD PLATED					1 PLACE	± 0.3	± ---	
3	4	INSERT, 4P FEMALE	PUR	BLACK					0 PLACE	± ---	± ---	
2	1	CABLE, 22-4, 300V, 105°C, PLTC	PVC JACKET	GRAY					ANGULAR ± 2 °			
1	1								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			
tb_frame_B_P_AM_T Rev E1 2012/01/25			9	8	7	6	5	4	3	2	1	SD-120065-062 1 OF 1

SEE CHART
B
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex](#):

[1200652213](#)