

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200652275

Status:

Active

Overview:

Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Description:

Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 4 Poles, Male (Straight) to Pigtail, 22 AWG, Black TPU WSOR Cable, 1.0m (3.28') Length



Documents:

Drawing (PDF)

Test Summary TS-120065-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	887191554891
Physical	
Cable Diameter	5.10mm (.201")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	46.750/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire Size AWG	22
Wire/Cable Type	UL 21215
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	60V
Material Info	
Engineering Number	804006B30M010
Reference - Drawing Numbers	
Sales Drawing	1200659964-000
Test Summary	TS-120065-001-001

EU ELV

Compliant with
Exemption 3

EU RoHS

Compliant with
Exemption 6(c)
REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead
Halogen-Free
Status
Not Relevant

For more information, please visit [Contact US](#)

China ROHS
ELV

China RoHS

Not Relevant
Compliant with
Exemption 3
Not Contained
CER_4000380980_00_000.pdf

RoHS Phthalates
ZZCERT_CE -
Declaration of
Conformity

Search Parts in this Series
120065 Series

This document was generated on 01/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200652275