

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200652283

Status:

Active

Overview:

Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Description:

Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Male (90°) to Pigtail, 22 AWG, Unshielded WSOR Cable, 1.0m (3.28') Length



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	887191554976
Physical	
Cable Diameter	4.80mm (.189")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-25° to +85°C
Wire Size AWG	22
Wire/Cable Type	WSOR
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	803007B30M010
Reference - Drawing Numbers	
Sales Drawing	SD-120065-075-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

120065 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200652283