

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200659211](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: Micro-Change (M12) Single-Ended Cordset, 5 Poles, Female (Straight) to Pigtail, 18 AWG, TPE Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [120065](#)
Connector End A Micro-Change (M12)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name Micro-Change (M12)
Region America
Type Single Ended
UPC 78172540935

Physical


Cable Diameter 6.86mm (.270")
Cable Length 1.0m (3.28')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket TPE
Material - Connector Body TPE
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Orientation Straight to Pigtail
Poles 5
Temperature Range - Operating -20° to +105°C
Wire Size AWG 18
Wire/Cable Type PLTC-ER

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 805000K03M010



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[120065](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200659211](#)