

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200659453](#)
Status: **Active**
Overview: Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Description: Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 8 Poles, Male (Straight) to Pigtail, 24 AWG, Unshielded WSOR Cable, 2.0m (6.56') Length



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Micro-Change (M12)
Region	Europe
Type	Single Ended
UPC	887191726540
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	17.393/g
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	24
Wire/Cable Type	UL 21215
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	30V
Material Info	
Engineering Number	808006B41M020
Reference - Drawing Numbers	
Sales Drawing	1200659964-00P, SD-120065-073-001

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Contained Per - D(2020)9139-DC (19 Jan 2021) Lead Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[120065](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120065-9453](#)