

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200660030

Status:

Active

Overview:

Brad Micro-Push M12 Cordsets and Connectors

Description:

Micro-Push (M12) Double-Ended Cordset, 3 Poles, Male (Straight)-to-Female (Straight), 22 AWG, Unshielded PVC Cable, 5.0m (16.40') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120066
Connector End A	Micro-Push (M12)
Connector End B	Micro-Push (M12)
IP Rating	IP65
Material - Contact	Copper Alloy
Overview	Brad Micro-Push M12 Cordsets and Connectors
Product Name	Micro-Push
Type	Double Ended
UPC	78678851899
Physical	
Cable Diameter	4.70mm (.185")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Push to Lock
Gender	Female-Male
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-25°C to +105°C
Wire Size AWG	22
Wire/Cable Type	Unshielded PVC
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	NN3030A41M050G
Reference - Drawing Numbers	
Sales Drawing	SD-120066-058

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120066 Series

Mates With

Micro-Change M12 Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120066-0030](#)