

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200660039](#)
Status: **Active**
Overview: [Brad Micro-Push M12 Cordsets and Connectors](#)
Description: Micro-Push (M12) Double-Ended Cordset, 4 Poles, Male (Straight)-to-Female (Straight), 22 AWG, Unshielded PVC Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family	Industrial Cordsets
Series	120066
Connector End A	Micro-Push (M12)
Connector End B	Micro-Push (M12)
IP Rating	IP65
Material - Contact	Copper Alloy
Overview	Brad Micro-Push M12 Cordsets and Connectors
Product Name	Micro-Push
Type	Double Ended
UPC	78678851903

Physical

Cable Diameter	4.70mm (.185")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Push to Lock
Gender	Female-Male
Keyway	A-coded
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25°C to +105°C
Wire Size AWG	22
Wire/Cable Type	Unshielded PVC

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	NN4030A41M050G
--------------------	----------------

Reference - Drawing Numbers

Sales Drawing	SD-120066-058
---------------	---------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
------------	--------------

ELV	Not Reviewed
-----	--------------

RoHS Phthalates	Not Reviewed
-----------------	--------------

Search Parts in this Series

[120066 Series](#)

Mates With

Micro-Change M12 Connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120066-0039](#)