

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200660442](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, PVC Cable, 15.0m (49.21') Length



Series image - Reference only

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [120066](#)
Connector End A Micro-Change (M12)
Connector End B Micro-Change (M12)
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name Micro-Change (M12)
Region America
Type Double Ended
UPC 78678830970

Physical

Cable Diameter 5.72mm (.225")
Cable Length 15.0m (49.21')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Orientation Straight to Straight
Poles 5
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 22
Wire/Cable Type UL 2661

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 885030A09M150

Reference - Drawing Numbers

Sales Drawing SD-120066-007-001

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant with
Exemption 3

Not Contained

Search Parts in this Series

[120066](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200660442](#)