

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200660887](#)
Status: **Active**
Overview:
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 18 AWG, TPE Cable, 3.0m (9.84') Length

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [120066](#)
Connector End A Micro-Change (M12)
Connector End B Micro-Change (M12)
IP Rating IP67
Material - Contact Brass
Overview microchange_m12_connectors
Product Name Micro-Change (M12)
Region America
Type Double Ended
UPC 78678837497

Physical

Cable Diameter 7.14mm (.281")
Cable Length 3.0m (9.84')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket TPE
Material - Connector Body TPE
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Net Weight 92.214/g
Orientation Straight to Straight
Poles 4
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 18
Wire/Cable Type PLTC/ITC

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 884030K03M030

Reference - Drawing Numbers

Sales Drawing 1200668165-000, SD-120066-020-001

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS 50 Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

[120066](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200660887](#)