

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200660891

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 18 AWG, TPE Cable, 4.0m (13.12') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E152210

General

Product Family

Industrial Cordsets

Series

120066

Connector End A

Micro-Change (M12)

Connector End B

Micro-Change (M12)

IP Rating

IP67

Material - Contact

Brass

Overview

Brad Micro-Change (M12) Connectors

Product Name

Micro-Change (M12)

Region

America

Type

Double Ended

UPC

78678837498

Physical

Cable Diameter

7.14mm (.281")

Cable Length

4.0m (13.12')

Color - Cable Jacket

Yellow

Coupling Style

Threaded

Gender

Female-Male

Keyway

Single

LED Indicator

No

Material - Cable Jacket

TPE

Material - Connector Body

TPE

Material - Coupling Nut

Nickel-plated Brass

Material - O-Ring

Fluoro-elastomer

Material - Plating Mating

Gold

Net Weight

154.110/g

Orientation

Straight to Straight

Poles

4

Temperature Range - Operating

-20°C to +105°C

Wire Size AWG

18

Wire/Cable Type

PLTC/ITC

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V AC/DC

Material Info

Engineering Number

884030K03M040

Reference - Drawing Numbers

Sales Drawing

1200668084-000, 1200668165-000,
SD-120066-020-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120066 Series

This document was generated on 08/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200660891