

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200675067](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: Micro-Change (M12) Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail with PNP LED Sensors, 0.34mm² PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
Series [120067](#)
Connector End A Micro-Change (M12)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name Micro-Change (M12)
Region Europe
Type Single Ended
UPC 883906318574

Physical

Cable Diameter 4.90mm (.193")
Cable Length 2.0m (6.56')
Color - Cable Jacket Black
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator PNP Sensors
Material - Cable Jacket PVC
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Net Weight 87.719/g
Orientation 90° to Pigtail
Poles 3
Temperature Range - Operating -30°C to +90°C
Wire Size AWG N/A
Wire/Cable Type UL 2464

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 30V AC/DC

Material Info

Engineering Number 8030P1E03M020

Reference - Drawing Numbers

Sales Drawing SD-120067-017-001, SD-120067-035-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120067](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200675067