

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1200680294

Status: **Active**

Overview: Brad Micro-Change (M12) Connectors

Description: Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 18 AWG PVC Cable, 0.50m Length

Documents:

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Tees and Splitters
Series	<u>120068</u>
IP Rating	IP67
Overview	<u>Brad Micro-Change (M12) Connectors</u>
Product Name	Micro-Change (M12)
Type	Splitter - Solid Body
UPC	78678804350

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	No
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	22.679/g
Poles	4
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25°C to +90°C

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number 081204EMF00000

Reference - Drawing Numbers

Sales Drawing 1200680294-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120068 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120068-0294