

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200720250](#)
Status: **Active**
Overview:
Description: Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 22 AWG, PVC Cable, 1.83m (6.0') Length

Agency Certification

CSA	LR6837
UL	E152210

General

Product Family	Industrial Cordsets
Series	120072
Connector End A	Micro-Change (1/2" - 20 UNF)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	microchange_m12_connectors
Product Name	Micro-Change (1/2" - 20 UNF)
Protocol	PROFIBUS
Region	America
Type	Single Ended
UPC	78678875912

Physical

Cable Diameter	5.72mm (.225")
Cable Length	1.83m (6.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Dual
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	98.883/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	22
Wire/Cable Type	UL 2661

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	703001D02F060
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-120072-010-001
---------------	-------------------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[120072](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200720250](#)